

Molift Mover 180

THE MOLIFT MOVER 180 IS A LIGHTWEIGHT AND COMPACT HOIST, SUITABLE BOTH IN HOME CARE AND INSTITUTIONAL ENVIRONMENTS

An everyday favourite

The Molift Mover 180 has a lightweight aluminium construction that makes the hoist very easy to manoeuvre. The large hoisting interval, 27–163 cm (10.4"–64.2"), allows hoisting from high surfaces as well as hoisting from the floor. Molift Mover 180 has also the option of 2- or 4-point suspension.

Ergonomic handling

For improved caregiver ergonomics, the Molift Mover 180 is equipped with Molift's unique push bar that provides multiple and flexible grip possibilities for improved caregiver ergonomics.

Molift Mover 180 is equipped with 75 mm castors as standard, but it is also available with 100 mm castors.

Molift Mover 180, like all Molift hoists, is equipped with the unique service notification system that notifies when service is required. The integrated service software can also be used to retrieve data about hoist usage and hoisting patterns.



Find optional suspensions and detailed information at page 26–27.

<p>Description</p> <p>Molift Mover 180 excl. suspension: 18000</p> <p>Molift Mover 180 with 100 mm castors excl. suspension: 18003</p> <p>Material Aluminium, Steel</p> <p>Service Software Included</p> <p>Total weight 32 kg (70.5 lbs)</p> <p>Length 1260 mm (49.6")</p>	<p>Item no.</p> <p>18000</p> <p>18003</p>	<p>Width chassis/legs outer 670 mm (26.3")</p> <p>Width open legs inner 1025 mm (40.4")</p> <p>Hoisting height 4-point suspension 265–1630 mm (10.4"–64.2")</p> <p>Hoisting interval 1365 mm (53.7")</p> <p>Leg height 105 mm (4.13")</p>	<p>Battery NiMH 14.4 V – 2.2 Ah Item no. 054100</p> <p>Battery charge time Approx. 3 hours</p> <p>Wheel size 7.5 cm (3")</p> <p>Hoisting speed 40 mm/sec (1.6"/sec)</p> <p>Rated performance 50 hoists at 75 kg and 50 cm (165 lbs and 19.7")</p>	<p>Cleaning instructions Use pH-neutral cleaning agents. If disinfection is required, use isopropyl alcohol. Do not use abrasive or corrosive substances for cleaning.</p>
--	--	--	--	---



Features



Unique push bar

The unique push bar provides the best natural grip, creating good ergonomics and many grip possibilities.



Easy to manoeuvre

Molift Mover 180 has a total weight of only 32 kg (70.5 lbs) which, together with the design, makes it easy to manoeuvre.



Molift Service Tool

Automatic service notification system determines when the hoist requires service and maintenance.



Many options

Mover 180 can be used with both a 2-point and a 4-point suspension. They come in six variants and can be interchanged easily without tools.



Weight scale

The Molift Mover 180 scale is approved Class III and complies with all technical standards. It can also calculate BMI (Body Mass Index) with a simple touch.

Molift Mover 180 has a large hoisting span that allows hoisting from the floor as well as high surfaces.

